

Supplementary Information

Multifunctional reduced graphene oxide coated clothes for oil/water separation and antibacterial application

Ravi Kant Upadhyay^a, Amrita Dubey^b, Prashant R. Waghmare^c, Richa Priyadarshini^b, and Susanta Sinha Roy^{d*}

^a. *Department of Chemistry, School of Natural Sciences, Shiv Nadar University, Gautam Budh Nagar 201314, Uttar Pradesh, India.*

^b. *Department of Life Sciences, School of Natural Sciences, Shiv Nadar University, Gautam Budh Nagar 201314, Uttar Pradesh, India.*

^c. *Department of Mechanical Engineering, University of Alberta, Edmonton, Canada T6 G 2G8*

^d. **Department of Physics, School of Natural Sciences, Shiv Nadar University, Gautam Budh Nagar 201314, Uttar Pradesh, India.*

Physical parameters of clothes

Weight of clothes:

Weight of 2x2 cm sparse cloth piece = 61.5 mg

Weight of 2x2 cm dense cloth piece = 14.2 mg

Water absorption capacity:

Pristine dense cloth: 11.063 g/g

Pristine sparse cloth: 1.8975 g/g

Diameter of fibers:

Pristine dense cloth: ~12 μm

Pristine sparse cloth: ~18.5 μm

Percentage increase in weight after 20 times deposition of GO:

Dense cloth: 20%

Sparse cloth: 4.33%

XPS analysis of pristine dense cloth (cloth-A) and sparse cloth (cloth-B)




Figure S1 XPS of Uncoated cloth samples

Table-1 Atomic percentage of C and O in uncoated cloth samples

Sample name	C (%)	O (%)
Dense cloth (Cloth-A)	80.86	19.14
Sparse cloth (Cloth-B)	78.93	21.07

XRD analysis of the pristine cloth




Figure S2 XRD of pristine cloth samples

XRD patterns of pristine clothes exhibit three common major peaks at 17.5, 22.6 and 25.8° suggesting that both cloth samples have same crystalline nature.