## **Supporting information**

## Co<sub>5.47</sub>N loaded N-doped carbon as an efficient bifunctional oxygen electrocatalyst for Zn-air battery

Zichao Rong<sup>a</sup>, Chenlong Dong<sup>a</sup>, Shaoning Zhang<sup>b</sup>, Wujie Dong<sup>b\*</sup>, Fuqiang Huang<sup>a, b\*</sup>

<sup>a</sup> State Key Laboratory of Rare Earth Materials Chemistry and Applications, College of Chemistry

and Molecular Engineering, Peking University, Beijing 100871, P.R. China;

<sup>b</sup> State Key Laboratory of High Performance Ceramics and Superfine Microstructure, Shanghai

Institute of Ceramics, Chinese Academy of Sciences, Shanghai 200050, P.R. China.

\* Corresponding author, E-mail addresses: dongwujie0219@163.com, huangfq@pku.edu.cn



Figure S1. XRD patterns of (a) CoNMC-600-1, (b) CoNMC-800-1 and (c) CoNMC-900-1.



**Figure S2.** N<sub>2</sub> absorption isotherm and pore distribution calculated from the desorption branch of (a) CoNMC-600-1, (b) CoNMC-800-1 and (c) CoNMC-900-1.



Figure S3. XPS survey spectra of CoNMC600-1, NMC-700, CoNMC-700-1, CoNMC-800-1 and CoNMC-900-1.



**Figure S4.** (a) LSV curves of CoNMC-700 in O<sub>2</sub>-saturated 0.1 M KOH. (b) CV curves of CoNMC-700-1 in N<sub>2</sub> or O<sub>2</sub>-saturated 0.1 M KOH. (c) Polarization curve of Pt/C before and after long-term cyclic measurements. (d) Polarization curve of CoNMC-700-1 before and after long-term cyclic measurements (graphite plate as counter electrode).



Figure S5. (a) Nyquist plots of CoNMC-600-1, CoNMC-700-1, CoNMC-800-1 and CoNMC-900-1.

(b) XPS spectra of CoNMC-700-1 before and after 2 h OER.



Figure S6. Photograph of the Pt/C-RuO<sub>2</sub> based Zn-air battery exhibiting an open circuit voltage of

1.497 V measured with a voltammeter.