

Supporting Information

Te microwire/2D Organic-inorganic Hybrid Perovskite Heterojunction Self-Powered Polarization Photodetector for Imaging and Communication Encoding

Yuxin Huang,^a Pengfan Li,^a Xuewei Yu,^a Lin Sun,^a Yanfeng Jiang^a and Pingping Yu

^{*a,b}

^a School of Integrated Circuits, Jiangnan University, Wuxi 214122, China;

^b Jiangsu Provincial Key Laboratory of MEMS Sensors and ASIC Manufacturing
Technology, Wuxi 214401, China

E-mail: pingpingyu@jiangnan.edu.cn




Fig. S1 Diagram of crystal packing for EMPC3.

Table S1

n value	General chemical formula	Structure Name	Inorganic layer thickness	Organic interlayer	Interlayer cation
1	EMPC1	Single-layer perovskite	Single-layer [PbCl ₆] ⁴⁻	EA ⁺	—
2	EMPC2	Double-layer perovskite	Double-layer [PbCl ₆] ⁴⁻	EA ⁺	MA ⁺
3	EMPC3	Three-layer perovskite	Three-layer [PbCl ₆] ⁴⁻	EA ⁺	MA ⁺




Fig. S2 Rise and fall time of EMPC3 PD at 1.2V (a) and rise and fall time of Te/EMPC3 PD at 0V (b).




Fig. S3 Schematic representation of the actual light area of the EMPC3 (a) and the Te/EMPC3 heterojunction (b).

Table S2 The light intensity at different wavelength.

Wavelength (nm)	Light Intensity (mW cm ⁻²)
280	0.40
368	1.32
410	1.24
500	1014
806	0.69
1006	0.71




Fig. S4 I-t curves of Te/EMPC3 PD at 368 nm, 0 V, 25 °C, under -10 V (a) and 10 V (b) pre-polarization as function of power density.




Fig. S5 The Fermi level of Te (a) and EMPC3 (b). (c) Calculated electronic band structure of the Te.




Fig. S6 Polar plot of the angle-resolved photocurrent of Te.




Fig. S7 Under 368 nm with the polarization direction rotated 360°, the angle-resolved photocurrent of the Te/EMPC3 device at -5 V (a) and 5 V (b) is represented in polar coordinates. Anisotropy ratio of Te/EMPC3 device under different bias voltages (c).

Table S3 The letter N corresponds to the actual electrode array current values at 0° and 90°, respectively.

0°	Row 1	Row 2	Row 3	Row 4	Row 5	Row 6
Column 1	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9
Column 2	2.01421E-9	2.46913E-6	2.01421E-9	2.01421E-9	2.46913E-6	2.01421E-9
Column 3	2.01421E-9	2.46913E-6	2.46913E-6	2.01421E-9	2.46913E-6	2.01421E-9
Column 4	2.01421E-9	2.46913E-6	2.01421E-9	2.46913E-6	2.46913E-6	2.01421E-9
Column 5	2.01421E-9	2.46913E-6	2.01421E-9	2.01421E-9	2.46913E-6	2.01421E-9
Column 6	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9

90°	Row 1	Row 2	Row 3	Row 4	Row 5	Row 6
Column 1	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9
Column 2	2.01421E-9	8.33E-7	2.01421E-9	2.01421E-9	8.33E-7	2.01421E-9
Column 3	2.01421E-9	8.33E-7	8.33E-7	2.01421E-9	8.33E-7	2.01421E-9
Column 4	2.01421E-9	8.33E-7	2.01421E-9	8.33E-7	8.33E-7	2.01421E-9
Column 5	2.01421E-9	8.33E-7	2.01421E-9	2.01421E-9	8.33E-7	2.01421E-9

Column 6	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9	2.01421E-9
-----------------	------------	------------	------------	------------	------------	------------