

Supplementary Information

Block sequence affects thermosensitivity and nano-assembly:

PEG-*L*-PA-*DL*-PA and PEG-*DL*-PA-*L*-PA block copolymers

Soo Hyun Park, Bo Gyu Choi, Hyo Jung Moon, So-Hye Cho, and Byeongmoon Jeong*

Fig. S1. CD spectra of PEG-*L*-PA-*DL*-PA (a) and PEG-*DL*-PA-*L*-PA (b) aqueous

solutions as a function of concentration at 20 °C.




Fig. S2. Apparent size of PEG-*DL*-PA-*L*-PA studied by dynamic light scattering of aqueous solution (1.0 wt. %) at 30 °C. The detector angle was 150° to the incident beam.

